

V7-3S17E9

([Home](#) : [Products](#) : [Sw itches](#) : [MICRO SWITCH™ Basic Sw itches](#) : [Premium V-Basic Sw itches](#) : [V7](#))



V7 Series Miniature Basic Switch, Single Pole Double Throw Circuitry, 100 mA at 125 Vac, Pin Plunger Actuator, 0,49 N [1.76 oz] Maximum Operating Force, Gold Contacts, Quick Connect Termination, CSA, UL

[click here to download Hi-Res image](#)

Actual product
appearance may vary.

Product Specifications

Sw itch Type	MICRO SWITCH™ Miniature 15,9 mm H x 10,2 mm W x 28,8 mm L [0.63 in H x 0.4 in W x 1.14 in L]
Sealed	No
Ampere Rating	0.1 A
Circuitry	SPDT
Actuator	Pin Plunger
Termination	Quick Connect
Operating Temperature	-40 °C to 82 °C [-40 °F to 180 °F]
Voltage	125 Vac
Contact Type	Gold-Plated Silver
Operating Force (OF)	0,49 N [1.7 oz] max.
Release Force	0,05 N [0.18 oz] min.
Pretravel (PT)	1,19 mm [0.047 in] max.
Overtravel (OT)	1,27 mm [0.050 in] min.
Differential Travel (DT)	0,05 mm to 0,25 mm [0.002 in to 0.010 in] max.
Housing Material	PCT Polyester Thermoplastic
Agency Approvals and Standards	UL, CSA, ENEC
Mounting Centers	22,2 mm [0.88 in]
Tightening Torque	0,56 N m [5.0 in lb]
Weight	8 g [0.3 oz]
Package Height	15,9 mm [0.63 in]
Package Width	10,3 mm [0.40 in]
Package Length	27,8 mm [1.09 in]
Comment	UL: E12252; CSA: LR41370
Availability	Global
UNSPSC Code	39122209
UNSPSC Commodity	39122209 Snap sw itches
Series Name	V7

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[V7-3S17E9](#)