

## SZL-VL-C

( Home : Products : Sw itches : MICRO SWITCH™ Limit Sw itches : MICRO SWITCH™ Global Limit Sw itches : SZL-VL )



Actual product appearance may vary.

**General Purpose Lim it Switch, VL Series; Side Rotary/Rod Adjustable; 1NC 1NO SPDT; Double Break**



SZL-VL-C  
highres photo



SZL-VL-C  
low res photo

### Product Specifications

Availability	North-America; Asia-Pacific
Operating Force (OF)	2 N to 7,84 N [0.45 lb to 1.76 lb] max.
Release Force	0,12 N - 0,49 N [0.026 lb - 0.11 lb] min.
Pretravel (PT)	20° max.
Overtravel (OT)	75° min.
Differential Travel (DT)	10° max.
Product Type	Miniature Limit Sw itches
Actuator	Side Rotary - Rod Adjustable
Lever Type	None
Circuitry	1NC 1NO SPDT Double Break
Ampere Rating	5.0 A/0.4 A
Supply Voltage	250 Vac/125 Vdc max.
Housing Material	Zinc Die-Cast/Plastic
Termination Type	Cable Gland
Series Name	SZL-VL
Shock	10 g max.
Vibration	55 Hz at double amplitude of 1,5 mm
Sealing	IP64
UL File #	E150950
Expected Mechanical Life	up to 10 Million
Operating Temperature	-20 °C to 60 °C [-4 °F to 140 °F]
Agency Approvals and Standards	UL, cULus, CE
Sealed	Industrial

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[SZL-VL-C](#)