

SL1-PK

([Home](#) : [Products](#) : [Sw itches](#) : [MICRO SWITCH™ Limit Sw itches](#) : [MICRO SWITCH™ Medium-Duty Limit Sw itches](#) : [SL1](#))



Series SL1: Top Roller Arm; 1 NC 1 NO Snap action; Gold contacts; Compression fitting

Actual product appearance may vary.

Product Specifications

Availability	North America; Asia-Pacific; Latin America
Operating Force (OF)	3,92 N [0.88 lb] max.
Release Force	0,79 N [0.79 lb] min.
Pretravel (PT)	2,0 mm [0.08 in] max.
Overtravel (OT)	4,0 mm [0.158 in] max.
Differential Travel (DT)	0,3 mm [0.012 in] max.
Product Type	MICRO SWITCH™ Miniature Limit Sw itches
Actuator	Top Roller Arm
Lever Type	None
Circuitry	1NC 1NO SPDT Snap Action
Ampere Rating	0.1 A
Supply Voltage	125 Vac/30 Vdc
Housing Material	Zinc Die-Cast
Termination Type	Cable Gland
Series Name	SL1
Sealing	IP67; NEMA 3, 4, 13
Operating Temperature	0 °C to 70 °C [35 °F to 160 °F]
Comment	M3 Terminal screw s; 5,8 mm to 9,6 mm outside cable diameter; Gold contacts
Sealed	Industrial
Contact Material	Gold

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[SL1-PK](#)