

BZE7-2RN18-PG

([Home](#) : [Products](#) : [Switches](#) : [MICRO SWITCH™ Limit Switches](#) : [MICRO SWITCH™ Medium-Duty Limit Switches](#) : [E7/V7](#))



Enclosed Switches Series E7: Wobble - Coil Spring Actuator; 1NC 1NO SPDT Snap Action; 20 mm [0.79 in] conduit

Actual product appearance may vary.

Product Specifications

Availability	Global
Operating Force (OF)	1,95 N [7 oz] max.
Pretravel (PT)	15° max.
Product Type	Enclosed Switches
Actuator	Wobble - Coil Spring
Circuitry	1NC 1NO SPDT Snap Action
Ampere Rating	15 A Ind./0.5 A Res./0.25 A Res.
Supply Voltage	125 Vac, 250 Vac, 480 Vac/125 Vdc/250 Vdc
Housing Material	Aluminum Die-Cast
Termination Type	PG13,5
Housing Type	Split Housing, Side Mount
Series Name	E7/V7
Sealing	IP65
Operating Temperature	-30 °C to 71 °C [-22 °F to 160 °F]
Comment	With seal boot on plunger
UNSPSC Code	39122213
UNSPSC Commodity	39122213 Limit Switches
Sealed	Industrial

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[BZE7-2RN18-PG](#)