

**BZE6-2RN221**

 ( [Home](#) : [Products](#) : [Switches](#) : [MICRO SWITCH™ Limit Switches](#) : [MICRO SWITCH™ Medium-Duty Limit Switches](#) : [E6/V6](#) )


**Enclosed Switches Series E6: Top Roller Arm Actuator, Adjustable with Steel Roller; 1NC 1NO SPDT Snap Action; 0.5 in - 14NPT conduit**

[click here to download Hi-Res image](#)

Actual product appearance may vary.

**Product Specifications**

Availability	Global
Operating Force (OF)	3,89 N to 7,23 N [14 oz to 26 oz]
Release Force	2,78 N [10 oz] min.
Pretravel (PT)	4,78 mm [0.188 in] max.
Overtravel (OT)	5,56 mm [0.219 in] min.
Differential Travel (DT)	0,15 mm [0.006 in] max.
Product Type	Enclosed Switches
Actuator	Top Roller Arm
Lever Type	Roller - Adjustable
Circuitry	1NC 1NO SPDT Snap Action
Ampere Rating	15 A Ind./2 A Ind./0.5 A Res./0.25 A Res.
Supply Voltage	125 Vac, 250 Vac, 480 Vac/600 Vac/125 Vdc/250 Vdc
Housing Material	Zinc Die-Cast
Termination Type	0.5 in - 14NPT Conduit
Housing Type	Split Housing, Side Mount
Series Name	E6/V6
Sealing	IP66; NEMA 1, 3, 4
UL File #	E12252
Operating Temperature	-32 °C to 71 °C [-25 °F to 160 °F]
Comment	With seal boot on plunger; Lever field adjustable 360° horizontally and 225° vertically
Agency Approvals and Standards	UL, CSA
UNSPSC Code	39122213
UNSPSC Commodity	39122213 Limit Switches
Sealed	Industrial

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[BZE6-2RN221](#)