

BZ-2RN-A2

([Home](#) : [Products](#) : [Switches](#) : [MICRO SWITCH™ Basic Switches](#) : [Premium Large Basic Switches](#) : [BZ/BA/WA/YZ](#))



BZ Series Standard Basic Switch, Single Pole Double Throw Circuitry, 15 A at 250 Vac, High Overtravel Plunger Actuator, Screw Termination, Silver Contacts, UL, CSA, ENEC

[click here to download Hi-Res image](#)

Actual product appearance may vary.

Product Specifications

Switch Type	MICRO SWITCH™ Standard 25,4 mm H x 17,8 mm W x 50,8 mm L [1.0 in H x 0.7 in W x 2.0 in L]
Sealed	No
Ampere Rating	15 A
Circuitry	SPDT
Actuator	High Overtravel Plunger
Termination	Screw
Operating Temperature	-55 °C to 85 °C [-67 °F to 185 °F]
Voltage	250 Vac
Contact Type	Silver
Operating Force (OF)	2,50 N to 3,61 N [9 oz to 13 oz] max.
Release Force	1,11 N [4.0 oz] min.
Overtravel (OT)	5,56 mm [0.219 in] min.
Differential Travel (DT)	0,01 mm to 0,05 mm [0.0004 in to 0.0020 in]
Material	Plastic
Housing Material	General Purpose Phenolic
Agency Approvals and Standards	UL, CSA, ENEC
Mounting Screw Size	3,53 mm [0.139 in]
Mounting Centers	25,4 mm [1 in]
Tightening Torque	0,33 N m [3.0 in lb]
Weight	24,94 g to 34,01 g [0.055 lb to 0.075 lb]
Package Height	24,1 mm [0.95 in]
Package Width	17,5 mm [0.69 in]
Package Length	49,3 mm [1.94 in]
Comment	CE: 61058-1; UL: E12252; CSA: LR41370; Bottom facing #6 screws and cup washers
Availability	Global
UNSPSC Code	39122209
UNSPSC Commodity	39122209 Snap switches
Series Name	BZ/BA/WA/YZ

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[BZ-2RN-A2](#)