

62NT1-3-NH

(Home : Products : basics : Sw itches : MICRO SWITCH™ Toggle Sw itches : NT)



NT Series Toggle Switch, Panel stand-off feature, 2 pole step base, 2 position, Screw terminal, Standard Lever

Actual product appearance may vary.

Product Specifications

Product Type	MICRO SWITCH™ Toggle Sw itch
Ampere/Voltage Range (Resistive Load)	0.5 A to 20 A at 0.5 Vdc to 28 Vdc 0.75 A at 115 Vdc 0.5 A to 15 A at 0.5 Vac to 277 Vac 0.5 A at 250 Vdc
Circuitry	DPDT
Action	2 position
Circuitry/Operating action	<div style="display: flex; justify-content: space-around;"> <div style="text-align: center;"> <p>Keyway Position</p> </div> <div style="text-align: center;"> <p>Opposite Keyway Position</p> </div> </div>
Mounting	Bushing 15/32 in
Termination	Screw
Lever Type	Standard
UL/CSA	L191: 15 A-125, 250, 277 Vac; 1/2 Hp-125 Vac; 1 Hp-250, 277 Vac; 5 A-120 Vac "L"
Comment	Panel stand-off feature; Thermoplastic case; No hardware
Availability	Global
UNSPSC Code	39122211
UNSPSC Commodity	39122211 Toggle Sw itch
Series Name	NT

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[62NT1-3-NH](#)