

31NT391-3-C08



([Home](#) : [Products](#) : [basics](#) : [Sw itches](#) : [MICRO SWITCH™](#) [Toggle Sw itches](#) : [NT](#))



NT Series Toggle Switch, 1 pole, 2 position, Quick Connect terminal, Tab Lever

Actual product appearance may vary.

Product Specifications

Product Type	MICRO SWITCH™ Toggle Sw itch
Ampere/Voltage Range (Resistive Load)	0.5 A to 20 A at 0.5 Vdc to 28 Vdc 0.5 A at 250 Vdc 0.75 A at 115 Vdc 0.5 A to 15 A at 0.5 Vac to 277 Vac
Circuitry	SPDT
Action	2 position
Circuitry/Operating action	Keyway Position  Opposite Keyway Position 
Mounting	Bushing 15/32 in
Termination	Quick Connect
Lever Type	Tab
UL/CSA	L191: 15 A-125, 250, 277 Vac; 1/2 Hp-125 Vac; 1 Hp-250, 277 Vac; 5 A-120 Vac "L"
Comment	Yellow
Availability	Global
UNSPSC Code	39122211
UNSPSC Commodity	39122211 Toggle Sw itch
Series Name	NT

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[31NT391-3-C08](#)