

22AC2-UL

([Home](#) : [Products](#) : [Sw itches](#) : [MICRO SWITCH™ Basic Sw itches](#) : [Standard Miniature and Subminiature Sw itches](#) : [AC](#))



Actual product appearance may vary.

AC Series Door Switch, Single Pole Double Throw Circuitry, 15 A at 250 Vac, Rod Actuator, Silver Contacts, Screw Termination, UL/CSA



22AC2-UL
highres photo



22AC2-UL
low res photo

Product Specifications

Switch Type	Door 38,1 mm H x 12,7 mm W x 38,1 mm L [1.5 in H x 0.5 in W x 1.5 in L]
Sealed	No
Ampere Rating	15 A
Circuitry	SPDT
Actuator	Rod
Termination	Screw
Operating Temperature	-18 °C to 82 °C [-65 °F to 180 °F]
Voltage	250 Vac
Contact Type	Silver
Operating Position (OP)	5,16 mm [0.203 in] min.
Free Position (FP)	9,53 mm [0.375 in] max.
Housing Material	Stainless Steel Bracket, Polyester Rod
Agency Approvals and Standards	UL, CSA
Weight	34,02 g [.075 lb]
Package Height	39,9 mm [1.57 in]
Package Width	13,2 mm [0.52 in]
Package Length	50,0 mm [1.97 in]
Availability	Global
UNSPSC Code	39122209
UNSPSC Commodity	39122209 Snap sw itches
Series Name	AC

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[22AC2-UL](#)