

14CE1-7

(Home : Products : Sw itches : MICRO SWITCH™ Limit Sw itches : MICRO SWITCH™ Medium-Duty Limit Sw itches : 14CE)



Miniature Enclosed Switches Series 14CE: Top Plunger; 1NC 1NO SPDT Snap Action; 7 m Cable

Actual product appearance may vary.

Product Specifications

Availability	Europe; Asia-Pacific
Operating Force (OF)	11,8 N [2.65 lb] max.
Release Force	4,4 N [0.99 lb] max.
Pretravel (PT)	1,0 mm ±0,5 mm [0.04 in ±0.02 in]
Overtravel (OT)	3,0 mm [0.118 in] min.
Differential Travel (DT)	0,1 mm [0.004 in] max.
Product Type	MICRO SWITCH™ Miniature Limit Sw itches
Actuator	Top Plunger
Lever Type	None
Circuitry	1NC 1NO SPDT Snap Action
Ampere Rating	5 A (Thermal)
Supply Voltage	240 Vac
Housing Material	Zinc Die-Cast
Termination Type	7 m Cable
Series Name	14CE
Sealing	IP65, NEMA 1, 3
UL File #	E41859
Expected Mechanical Life	up to 10 Million
Operating Temperature	0 °C to 70 °C [35 °F to 160 °F]
Comment	Bottom Exit Cable
Agency Approvals and Standards	CE. IEC947-5-1, EN60947-5-1
UNSPSC Code	39122213
UNSPSC Commodity	39122213 Limit Sw itches
Sealed	Industrial

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[14CE1-7](#)