

**6AS5**

( [Home](#) : [Products](#) : [Sw itches](#) : [MICRO SWITCH™ Basic Sw itches](#) : [Standard Miniature and Subminiature Sw itches](#) : [AS](#) )

Image Not Available

**AS Series Tandem Switch, Single Pole Double Throw Circuitry (2 CKT), 15 A at 250 Vac, Flexible Leaf Actuator, Silver Contacts, Screw Termination**

Actual product appearance may vary.

**Product Specifications**

Sw itch Type	MICRO SWITCH™ Standard 19,0 mm H x 35,1 mm W x 49,3 mm L [.75 in H x 1.38 in W x 1.4 in L]
Sealed	No
Ampere Rating	15 A
Circuitry	2 CKT SPDT
Actuator	Flexible Leaf
Termination	Screw
Operating Temperature	-55 °C to 85 °C [-67 °F to 185 °F]
Voltage	250 Vac
Actuator Length	38,4 mm [1.51 in]
Contact Type	Silver
Overtravel (OT)	0,76 mm to 1,52 mm [0.030 in to 0.060 in] min.
Material	Plastic
Housing Material	General Purpose Phenolic
Agency Approvals and Standards	UL, CSA
Mounting Screw Size	3,53 mm [0.139 in]
Mounting Centers	25,4 mm [1 in]
Tightening Torque	0,33 N m [3.0 in lb]
Weight	50 g to 70 g [0.11 lb to 0.15 lb]
Package Height	24,1 mm [0.95 in]
Package Width	35,1 mm [1.38 in]
Package Length	49,3 mm [1.94 in]
Recommended For	Tandem Sw itch Assemblies w ith single actuator
Comment	Centered Leaf. No adjustment. Sw itches operate w ithin .030" of each other.
Availability	Global
UNSPSC Code	39122209
UNSPSC Commodity	39122209 Snap sw itches
Series Name	AS

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[6AS5](#)