








WIRING TABLE

WIRE	CN1 TERMINAL NO.	COLOR	WIRING	Cable OPEN END
UL758 STYLE2464 (AWG #22) 5 TWISTED PAIRS	1	BLUE		OPEN
	2	WHITE		OPEN
	3	YELLOW		OPEN
	4	BROWN		OPEN
	5	GREEN		OPEN
	6	BLACK		OPEN
	7	RED		OPEN
	8	GRAY		OPEN
	9	PURPLE		OPEN
	10	ORANGE		OPEN

NOTE 1. INTENDED FOR PROTOTYPE AND TESTING PURPOSES.

NOTE 2. REFERENCE TERMINAL DRAWING AND SPECIFICATIONS FOR MORE DETAIL.


NOTE 3. 5 PAIRS OF TWISTED WIRES ARE INSIDE THE MULTI-CONDUCTOR CABLE.
SHIELD AND DRAIN WIRE ARE NOT INSIDE THE MULTI-CONDUCTOR CABLE.

NOTE 4. REFER TO THE WIRING TABLE FOR WIRE COLORS. SUBJECT TO CHANGE.

NOTE 5. TERMINAL CRIMPED ON ONE END OF WIRE ONLY. OPPOSITE END IS BLUNT CUT.

NOTE 6. THE CRIMPED WIRE SHOULD ONLY BE INSERTED TO THE SPECIFIED JAE HOUSING AND CAVITY.

NOTE 7. REFERENCE THE JAE SPECIFICATION AND INSTRUCTION MANUAL FOR PROPER HANDLING AND APPLICABLE HOUSING PART NUMBERS.

2	WIRE	—	UL758 STYLE2464 (AWG #22) (NOTE3)	COLOR:- (NOTE4)	—		
1	JN1-22-22S(-10000)	10	COPPER ALLOY	PLATING(MATING AREA):Au(0.1μm MIN) OVER Ni	SJ035504		
符号 NO.	名 称 DESCRIPTION	個 数 QTY.	材 料 MATERIAL	仕 上 FINISH	備 考 REMARKS		
仕様書 (SPECIFICATION) JACS-5111-＊ J A H L-5111-＊		第1版 (ORIGINAL DATE) 27/FEB/2024		尺度 (SCALE) 1:1	シリーズ (SERIES) JN1	日本航空電子工業株式会社 JAPAN AVIATION ELECTRONICS INDUSTRY, LTD.	SIZE A3
		製図 DR.	T. SHIODA	名称 (TITLE) C2777- JN1-22-22S- AWG22-900			
一般公差 (GENERAL TOLERANCE) 寸法 (DIMENSION)		担当 CHK.	T. SHIODA			図面番号 (DRAWING NO.) CAL24-015	
		査閲 APPD.	—				
角度 (ANGLES) . ±0.8 × ±0.4 .×× ±0.1 ××× ±		承認 APPD.	Y. TAKAGI	質量 (MASS)			
		単位 (UNIT): mm					シート (SHEET NO.) 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[JAE Electronics:](#)

[C2777-JN1-22-22S-AWG22-900](#)