






Rating	10A 250V AC 	Mounting Hole	Circuit Diagram
Insulation Resistance	DC 500V 100M ohm Min		Nil
Dielectric Strength	AC 1500V 1 minute		
Fuse Size	Ø6.35*31.8 Ø6.35*30		
			

Material:
Frame: PF,Black
Cover: PF,Black
Terminals: Nickel plated Brass



Tolerances ± 0.3 Unless Otherwise Specified

10/19/16	柳新強	依品管通知，刪除CSA安規符號				
12/28/13	柳新強	依品管及上級通知要求統一R3系列保險絲規格,保留原6.35*31.8mm,取消6.3*30mm,更改為6.35*30mm				
11/08/13	柳新強	修正Model No為R3-22A-02N-1N;依公司規定增加SCI LOGO,UL變更為CUL				
12/08/12	韓輝	側端子翹起角度修改為15°±10°				
Date	Name	Description				No.
Drawn	Checked	Approved	SCI BOM No.	1310096	Model Name	FUSE HOLDER
柳新強			Customer No.		Model No.	R3-22A-02N-1N
10/19/16		李元生	Unit	mm	Shin Chin Industrial Co., Ltd.	
						Rev. 4

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Shin Chin:](#)

[R3-22A](#)