




Rating	20A 250VAC		Mounting Hole	Circuit Diagram
Insulation Resistance	DC 500V 100M ohm Min.			Nil
Dielectric Strength	AC 1500V 1 minute			
Fuse Size	$\phi 6.35 \times 32 \text{mm}$ $\phi 6.4 \times 30 \text{mm}$			







Material:


Frame : NYLON#66,Black

Top cap : NYLON#66,Black

Terminals : Copper alloy, silver plated



Tolerances Unless Otherwise Specified ± 0.3

							△		
							△		
Date	Name	Description				No.			
Drawn	Checked	Approved	SCI BOM No	1310229	Model Name	FUSE HOLDER			
柳新強			Customer No	441-R355	Model No.	R3-55A	Rev.		
06/11/13		6/13-13	Unit	mm	Shin Chin Industrial Co., Ltd.				0

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Shin Chin:](#)

[R3-55A](#)