





Rating	30A max 12/24VDC	<div data-bbox="1034 293 1430 506" data-label="Image"> </div>
Insulation Resistance	DC 500V 100M ohm Min.	
Dielectric Strength	AC 1000V 1 minute	
Operation Temperature	-25°C~85°C	
Fuse Type	BLADE FUSE	

Note:

1. Terminal Push/Pull strength  $\geq 9.1$  Kgf.
2. With LED warning light when fuse is burned.



							△
							△
							△
							△
Date	Name	Description					NO
Drawn	Checked	Approved	SCI BOM No.	1310938	Model Name	FUSE HOLDER	
袁浩徐		<i>Simon</i>	Customer No.	112-R3-67L	Model No.	R3-67L	REV.
09/24/'19		10/8-'19	Unit	mm	SHIN CHIN INDUSTRIAL CO., LTD.		0

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Shin Chin:](#)

[R3-67L](#)