





Rating	10(4)A 125/250VAC 20A 14Vdc 10A 28Vdc	IP65 T85 	<div>Mounting Hole</div> <div></div> <div></div>
Contact Resistance	50m ohm Max.		
Insulation Resistance	DC 500V 100M ohm Min.		
Dielectric Strength	AC 1500V 1 minute		
Operation Temperature	-20°C~85°C		
Switch Function	3P SPDT ON-OFF-ON		



Material:

Frame: Black, Nylon 66 (94-V2)

Actuator: Black, PC (94-V2)




Waterproof rubber: Black, Silicone

Terminals: Silver plated, Copper alloy

Hot Stamping: White, I I O I

Waterproof: IP65

Circuit Diagram



Tolerances ± 0.3 Unless Otherwise Specified

3/20/18	林玗呈	依MCR#RAD20180201-095之需求更新安規			△	
Date	Name	Description			△	
Drawn	Checked	Approved	SCI BOM No.	1824142	Model Name	ROCKER SWITCH
林玗呈		王偉山	Customer No.		Model No.	R13-112D8-02
3/20/18		3/20/18	Unit	mm	Shin Chin Industrial Co., Ltd.	
						REV. 2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Shin Chin:](#)

[R13-112D8-02-BB](#)