







Rating	Input:9V~48V DC Voltage Tolerance: +/- 1% (0.1V @ 12V, 0.5V @ 48V) LED display. Reverse polarity protection Surge protection up to 400W/50V	Mounting Hole 
Insulation Resistance	DC 500V 100M $\Omega$ Min.	
Operating Temperature	-20℃~50℃	



Tolerances  $\pm 0.3$  Unless Otherwise Specified

12/14/16	方婷鳳	依電壓規格修正圖號,原圖號A25-1C-BB3-G,修正為A25-1C-BB4-G		Drawn	Checked	Approved	SCI BOM No.	1570019	Model Name	DC Voltmeter	
Date	Name	Description	No.	Rock Hsu			Customer No.		Model No.	A25-1C-BB4-G	Rev.
				12/14/16			Unit	mm		Shin Chin Industrial Co., Ltd.	1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Shin Chin:](#)

[A25-1C-BB4-G](#)