







Rating	Input: 9V-48V DC Voltage Tolerance: $\pm 1\%$ (0.1V @ 12V, 0.5V @ 48V) LED display. Reverse polarity protection Surge protection up to 400W/50V	Mounting Hole 
	Insulation Resistance	
	Operating Temperature	
	DC 500V 100M Ω Min.	
	-20°C~50°C	



Tolerances ± 0.3 Unless Otherwise Specified

				Drawn	Checked	Approved	SCI BOM No.	1570018	Model Name	DC Voltmeter	
				Rock Hsu			Customer No.		Model No.	A25-1C-BB4-U	Rev.
12/12/16	方婷鳳	依電壓規格修正圖號,原圖號A25-1C-BB3-U,修正為A25-1C-BB4-U		12/12/16			Unit	mm	Shin Chin Industrial Co., Ltd.		1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Shin Chin:](#)

[A25-1C-BB4-U](#)