







Rating	Input 6V~33V DC Voltage Tolerance: $\pm 1\%$ (0.1V @ 12V, 0.2V @ 24V) LED display. Reverse polarity protection Surge protection up to 400W/35V	Mounting Hole 
	Insulation Resistance	
	Operating Temperature	
	DC 500V 100M $\Omega$ Min.	
	-20 $^{\circ}$ ~50 $^{\circ}$	



Ground Tab  
Quick Terminal(.250")



Positive Tab  
Quick Terminal(.250")



Tolerances  $\pm 0.3$  Unless Otherwise Specified

Date	Name	Description	No.	Drawn	Checked	Approved	SCI BOM No.	1570001	Model Name	DC Voltmeter	
				Rock Hsu	105.1.04	蘇承民	Customer No.		Model No.	A25-1-BB3-R	Rev.
				12/31/15			Unit	mm	Shin Chin Industrial Co., Ltd.		0

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Shin Chin:](#)

[A25-1-BB3-R](#)