


Rating	60A max 12V DC	 $\phi 15.875$ [0.625]	
Contact Resistance	50m ohm Max.		
Insulation Resistance	DC 500V 100M ohm Min.		
Dielectric Strength	AC 1500V 1 minute		
Switch Function	2P PUSH OFF-(ON)		



- Heavy duty die cast construction with rubber boot seal(Black/Red, EPDM material).
- Cycle brass pillar terminals.
- The mmns no indication tolerance is ± 0.3 and the inlbs is ± 0.012 .

SCI BOM No.	Rubber boot seal	Model No.
1110067	Black	A2-19A-14-A1
1110070	Red	A2-19A-14-A2

						△
						△
						NO
Date	Name	Descriptions				
Drawn	Checked	Approved	SCI BOM No.	See table	Model Name	Starter Button Switch
李国良	<i>[Signature]</i>	<i>[Signature]</i>	Customer No.		Model No.	A2-19A-14-A1/A2 REV.
11/10/08	7/6-09	7/20-09	Unit	mm(inch)	SHIN CHIN INDUSTRIAL CO., LTD. 0	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Shin Chin:](#)

[A2-19A-14-A1](#)