





| | | | |
|-----------------------|-----------------------|---|---|
| Rating | 60A max 12V DC |  #15.87531 [ø0.6251mm] |  |
| Contact Resistance | 50m ohm Max. | | |
| Insulation Resistance | DC 500V 100M ohm Min. | | |
| Dielectric Strength | AC 1500V 1 minute | | |
| Switch Function | 2P PUSH OFF-(ON) | | |



- Heavy duty die cast construction with rubber boot seal(Black/Red, EPDM material) .
- Cycle brass pillar terminals .
- The mmns no indication tolerance is ± 0.3 and the inlbs is ± 0.012 .

| SCI BOM No. | Rubber boot seal | Model No. |
|-------------|------------------|--------------|
| 1110067 | Black | A2-19A-14-A1 |
| 1110070 | Red | A2-19A-14-A2 |

| | | | | | | | △ |
|----------|---------|--------------|--------------|-----------|--------------------------------|-----------------------|------|
| | | | | | | | △ |
| | | | | | | | NO |
| Date | Name | Descriptions | | | | | |
| Drawn | Checked | Approved | SCI BOM No. | See table | Model Name | Starter Button Switch | |
| 李强 | 王江 | 王江 | Customer No. | | Model No. | A2-19A-14-A1/A2 | REV. |
| 11/10/08 | 7/6-09 | 7/6-09 | Unit | mm(inch) | SHIN CHIN INDUSTRIAL CO., LTD. | | 0 |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Shin Chin:](#)

[A2-19A-14-A2](#)