





Rating	60A max 12V DC		
Contact Resistance	50m ohm Max.		
Insulation Resistance	DC 500V 100M ohm Min.		
Dielectric Strength	AC 1500V 1 minute		
Switch Function	2P PUSH OFF-(ON)		



- Heavy duty die cast construction with rubber boot seal(Black/Red, EPDM material) .
- Hexagon brass pillar terminals .
- The mmns no indication tolerance is ± 0.3 and the inlbs is ± 0.012 .

SCI BOM No.	Rubber boot seal	Model No.
1110068	Black	A2-19A-15-A1
1110071	Red	A2-19A-15-A2

									△
									△
Date	Name	Descriptions							NO
Drawn	Checked	Approved	SCI BOM No.	See table	Model Name	Starter Button Switch			
李日紅	李元生	Danny	Customer No.	112-A2-19-15-A2	Model No.	A2-19A-15-A1/A2			
11/10/'08	7/6/09'	7/7/09'	Unit	mm[inch]	SHIN CHIN INDUSTRIAL CO., LTD.				REV. 0

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Shin Chin:](#)

[A2-19A-15-A2](#) [A2-19A-15-A1](#)