





Rating	3A
Insulation Resistance	DC 500V 100M ohm Min.
Dielectric Strength	AC 1500V 1 minute
Operation Temperature	-20°C~+80°C
Color	Red



C8\R8\R8-122_1

									△
									△
Date	Name	Description							No.
Drawn	Checked	Approved	SCI BOM No.	1530071	Model Name	ALLIGATOR CLIPS			
袁浩徐	袁浩徐	李生	Customer No.	112-R8-122-R	Model No.	R8-122	Rev.		
06/01/'21	2021/06/08	2021/06/08	Unit	mm	Shin Chin Industrial Co., Ltd.				0

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Shin Chin:](#)

[R8-122-R](#)