

## Managed Layer 2 Gigabit Ethernet Switch

(20) 10/100/1000Base-T Ports + (4) 100/1000Base-X SFP/RJ-45 Combo Ports + (2) 100/1000Base-X SFP Slots



This switch is a high performance Layer 2 managed switch with 52Gbps switching capacity. It provides (20) 10/100/1000 copper ports, (4) 100/1000Base-X SFP/RJ-45 Combo Ports, and (2) 100/1000Base-X dual speed SFP slots.

### Ordering Information

#### SM24T6DPA

(20) 10/100/1000Base-T ports  
+ (4) 100/1000Base-X SFP/RJ-45 combo ports  
+ (2) 100/1000Base-X SFP slots  
(19" Rack Mount Brackets Included)

Optional Accessories (sold separately)

SFP Modules

### Features

- Support IPv4/IPv6 dual protocol stack
- Support Jumbo Frame up to 9K bytes
- Authentication – RADIUS IEEE 802.1X, TACACS+
- Security - Support SSH/SSL
- Port based or tagged (IEEE 802.1Q) VLAN, MAC based VLAN, Management VLAN and Private VLAN Edge
- DHCP Relay including option 82
- L2/L3/L4 ACLs Support MAC ACL, IP standard/extended ACL
- LLDP (Link Layer Discovery Protocol)
- IEEE 802.3az Energy Efficiency
- IP Source Guard, Port Security
- DHCP Server
- Device Management System (DMS): Graphic Monitoring, Grouping, Traffic Monitoring

### Specifications

Standards	IEEE 802.3 IEEE 802.3u IEEE 802.3z IEEE 802.3ab IEEE 802.3x IEEE 802.3ad IEEE 802.1D IEEE 802.1w IEEE 802.1s IEEE 802.1Q IEEE 802.1p IEEE 802.1ad IEEE 802.1X IEEE 802.3az
Connectors	(1) RJ console port (20) 10/100/1000 RJ-45 ports (4) 100/1000 SFP/RJ-45 combo ports (2) 100/1000 SFP slots
Protocols	CSMA/CD
Technology	Store-and-forward switching architecture
MAC Address	8K MAC address table
Backplane	52 Gbps
Dimensions	Width: 17.4" [442 mm] Depth: 8.3" [211 mm] Height: 1.73" [44 mm]
Power Input	100 - 240VAC
Environment	Operating: 0°C to 50°C Humidity: 5% to 90% (non-condensing)
Weight	5.3 lbs. [2.4 kg]
Certifications	Safety: IEC 62368-1/EN62368-1, UL Listed EMC: EN55022 Class A, IEC61000-3, EN55025, IEC61000-4, CISPR PUB.22 Class A, FCC Part 15, ICES-003 Class A
Warranty	Lifetime

### Software Features

- Management: Web Management, SNMP V1/V2c/V3, Telnet, CLI
- Port Trunk: Supports IEEE 802.3ad port trunk with link aggregation control protocol (LACP) and static trunk
- IGMP: Support IGMP Snooping V1/V2/V3, GVRP, IGMP Proxy, and IGMP Querier
- Quality of Service: Supports 8 egress queues per port enable differentiated management of up to 8 traffic types across the stack. Strict priority and WRR
- Spanning Tree: Supports IEEE 802.1s MSTP, IEEE 802.1w RSTP and IEEE 802.1D STP Compliant
- VLAN: Port Based VLAN, IEEE 802.1Q tag-based, up to 4k VLAN entries, QinQ, MAC-based VLAN, Private VLAN, Guest VLAN, Voice VLANs and Management VLAN
- IPv4 / IPv6 Static Routing
- Firmware Update, configure backup/restore through TFTP and HTTP

#### Power Cord Included

To order the corresponding country specific power cord, add the extension from the list below to the end of the SKU; Ex: SM24T6DPA-NA

#### -NA = Country Code

-NA = North America  
-LA = Latin America  
-EU = Europe  
-UK = United Kingdom  
-SA = South Africa  
-JP = Japan  
-OZ = Australia  
-BR = Brazil

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Lantronix:](#)

[SM24T6DPA-BR](#) [SM24T6DPA-EU](#) [SM24T6DPA-JP](#) [SM24T6DPA-LA](#) [SM24T6DPA-NA](#) [SM24T6DPA-OZ](#)  
[SM24T6DPA-SA](#) [SM24T6DPA-UK](#) [SM24T6DPA-BR-L1Y1](#) [SM24T6DPA-BR-L1Y3](#) [SM24T6DPA-BR-L1Y5](#)  
[SM24T6DPA-BR-L2Y1](#) [SM24T6DPA-BR-L2Y3](#) [SM24T6DPA-BR-L2Y5](#) [SM24T6DPA-EU-L1Y1](#) [SM24T6DPA-EU-L1Y3](#)  
[SM24T6DPA-EU-L1Y5](#) [SM24T6DPA-EU-L2Y1](#) [SM24T6DPA-EU-L2Y3](#) [SM24T6DPA-EU-L2Y5](#) [SM24T6DPA-JP-](#)  
[L1Y1](#) [SM24T6DPA-JP-L1Y3](#) [SM24T6DPA-JP-L1Y5](#) [SM24T6DPA-JP-L2Y1](#) [SM24T6DPA-JP-L2Y3](#) [SM24T6DPA-JP-](#)  
[L2Y5](#) [SM24T6DPA-L1Y1](#) [SM24T6DPA-L1Y3](#) [SM24T6DPA-L1Y5](#) [SM24T6DPA-L2Y1](#) [SM24T6DPA-L2Y3](#)  
[SM24T6DPA-L2Y5](#) [SM24T6DPA-LA-L1Y1](#) [SM24T6DPA-LA-L1Y3](#) [SM24T6DPA-LA-L1Y5](#) [SM24T6DPA-LA-L2Y1](#)  
[SM24T6DPA-LA-L2Y3](#) [SM24T6DPA-LA-L2Y5](#) [SM24T6DPA-NA-L1Y1](#) [SM24T6DPA-NA-L1Y3](#) [SM24T6DPA-NA-L1Y5](#)  
[SM24T6DPA-NA-L2Y1](#) [SM24T6DPA-NA-L2Y3](#) [SM24T6DPA-NA-L2Y5](#) [SM24T6DPA-OZ-L1Y1](#) [SM24T6DPA-OZ-](#)  
[L1Y3](#) [SM24T6DPA-OZ-L1Y5](#) [SM24T6DPA-OZ-L2Y1](#) [SM24T6DPA-OZ-L2Y3](#) [SM24T6DPA-OZ-L2Y5](#) [SM24T6DPA-](#)  
[SA-L1Y1](#) [SM24T6DPA-SA-L1Y3](#) [SM24T6DPA-SA-L1Y5](#) [SM24T6DPA-SA-L2Y1](#) [SM24T6DPA-SA-L2Y3](#)  
[SM24T6DPA-SA-L2Y5](#) [SM24T6DPA-UK-L1Y1](#) [SM24T6DPA-UK-L1Y3](#) [SM24T6DPA-UK-L1Y5](#) [SM24T6DPA-UK-L2Y1](#)  
[SM24T6DPA-UK-L2Y3](#) [SM24T6DPA-UK-L2Y5](#)