

## SUMMARY

### # Wires

Low	0
High	0
Coax	0
Triax	0
Quad	0
Fiber	0
Fluidic	0

*Image is for illustrative purpose only*

### Download

[Request a quote](#)

[Catalog](#)

Series	3K
Termination type	No contacts / Accessory
IP rating	61
Cable Ø	0.00 - 0.00 mm
Status	active
Alternative part	

## TECHNICAL DETAILS

### Mechanics

Shell Style/Model	BRR*: Cap spring loaded dust cap for ED and EB models
Keying	No keying
Housing Material	
Variant	G : Grey
Weight	7.56 g

### Performance

Configuration
Insulator
Rated Current

### Others

Endurance (Shell): 5000 mating cycles
Temp (min / max): -55°C / +200°C

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Axes material: Nickel-plated brass  
Maximum operating temperature: 100°C  
Watertightness: IP61 according to IEC 60529  
IP Rating: 61

---

## DRAWINGS

### Draws

No keying

### Dimensions

	A	B	C	L	M	N
mm.	29	29	23	8.1	3	33.2
in.	1,14	1,14	0,91	0,32	0,12	1,31

---

## RECOMMENDED BY LEMO

### Tools

None

### Cables

121 221			
131 221			

*LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.*

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[LEMO:](#)

[BRR.3K.200.PZSG](#)