

SUMMARY

Wires

Coax 1



Image is for illustrative purpose only

Series 01
Termination type Male solder
IP rating 50
AWG wire size 0.00 - 0.00
Cable Ø 0.00 - 0.00 mm
Status active

Download

[Request a quote](#)

[Catalog](#)

TECHNICAL DETAILS

Mechanics

Shell Style/Model FLH.01*: Elbow plug, non-latching, for cable crimping
Keying Circular, male
Housing Material Brass (gold plated [ISO 27874]) shell, collet nut, brass latch sleeve and mid pieces
Weight 2.11 g

Performance

Configuration 01.250 : 1 Coax (50 Ohm)
Insulator
Rated Current


Specifications

Contact Type: Solder

Others

Endurance (Shell): 1000 mating cycles

DRAWINGS



Dimensions

	A	H	L
mm.	6	14.5	11
in.	0,24	0,57	0,43

RECOMMENDED BY LEMO

Tools

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[LEMO:](#)

[FLH.01.250.DTAE31](#)