

## SUMMARY

### # Wires

Low voltage 7



Image is for illustrative purpose only

Series 1P  
Termination type Male solder  
IP rating 50  
AWG wire size 0.00 - 26.00  
Cable Ø 5.30 - 6.50 mm  
Status active  
Matching parts [PLB.M0.7GL.LA](#)

### Download

[Request a quote](#)

[Catalog](#)

## TECHNICAL DETAILS

### Mechanics

Shell Style/Model PA\*: Straight plug with cable collet and nut for fitting a bend relief  
Keying 2 keys (alpha=60; Plug: male contacts; Receptacle: female contacts)  
Housing Material PSU (Polysulfone), gray  
Variant A : Blue collet nut for bend relief

### Performance

Configuration 1P.M07 : 7 Low Voltage  
Insulator L: PEEK (UL 94 / V-0/1.5)  
Rated Current 5 Amps

### Specifications

Contact Type: Solder  
Contact Dia.: 0.7 mm (0.0275in)  
Bucket Dia.: 0.6 mm (0.024in)  
Max. Solid Conductor: 0.14 mm<sup>2</sup> (AWG 26)  
Max. Stranded Conductor: 0.14 mm<sup>2</sup> (AWG 26)  
R (max): 6.5 mOhm  
Test voltage (kV rms) Contact-contact: 1.05  
Air clearance min.: 0.85 mm  
Creepage distance min.: 0.85 mm

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

## Others

Endurance (Shell): >2000 mating cycles

Temp (min / max): -50°C / +150°C


F ret (min): 50 N

F ret (max): 150 N

Steam sterilization: > 100 times (with potting on rear connection)

---

## DRAWINGS



---

## RECOMMENDED BY LEMO

### Tools

### Cables

270250

PVC

Grey



LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[LEMO:](#)

[PAB.M0.7GL.AC65AZ](#)