

## SUMMARY

### # Wires

Low voltage 8



Image is for illustrative purpose only

Series	SP
Termination type	Male solder
IP rating	50
AWG wire size	30.00 - 22.00
Cable Ø	6.60 - 7.50 mm
Status	active
Matching parts	<a href="#">SRN.M08.GLL.7GZ</a>

### Download

[Request a quote](#)

[Eplan](#)

[Catalog](#)

## TECHNICAL DETAILS

### Mechanics

Shell Style/Model	SA/Z*: Straight plug, key (N) or keys (P, S and T), with cable collet and nut for fitting a bend relief
Keying	3 keys (alpha=0, gamma=30, plug: male contacts, receptacle: female contacts)
Housing Material	Proprietary sulfone, gray
Variant	GZ : Gray collet nut for bend relief
Weight	46.77 g

### Performance

Configuration	SP.M08 : 8 Low V.
Insulator	L: PEEK (UL 94 / V-0/1.5)
Rated Current	5.0 Amps

### Specifications

Contact Type: Solder  
Contact Dia.: 0.9 mm (0.0354in)  
Bucket Dia.: 0.8 mm (0.032in)  
Max. Solid Conductor: 0.36 mm<sup>2</sup> (AWG 23)  
Max. Stranded Conductor: 0.36 mm<sup>2</sup> (AWG 22)  
R (max): 8.5 mOhm

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.


Test voltage (kV rms) Contact-contact: 1.50  
Air clearance min.: 0.78 mm  
Creepage distance min.: 0.78 mm

## Others

Endurance (Shell): >2000 mating cycles  
Temp (min / max): -50°C / +170°C

---

## DRAWINGS



## Dimensions

	A	L
mm.	15.5	48
in.	0,61	1,89

---

## RECOMMENDED BY LEMO

### Tools

Crimp Tool: [DPC.91.701.V](#)

### Cables

108220	PVC	Black	
--------	-----	-------	---

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

*LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.*

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[LEMO:](#)

[SAN.M08.GLA.7GZ](#)