

SUMMARY

Wires

Low voltage 22



Image is for illustrative purpose only

Series SP
Termination type Male solder
IP rating 50
AWG wire size 36.00 - 28.00
Cable Ø 6.60 - 7.50 mm
Status active
Matching parts [SKN.M22.GLLA](#)

Download

[Request a quote](#)

[Catalog](#)

TECHNICAL DETAILS

Mechanics

Shell Style/Model SA/Z*: Straight plug, key (N) or keys (P, S and T), with cable collet and nut for fitting a bend relief
Keying 3 keys (alpha=0, gamma=30, plug: male contacts, receptacle: female contacts)
Housing Material Proprietary sulfone, gray
Variant A : Blue collet nut

Performance

Configuration SP.M22 : 22 Low V.
Insulator L: PEEK (UL 94 / V-0/1.5)
Rated Current 2.0 Amps

Specifications

Contact Type: Solder
Contact Dia.: 0.5 mm (0.0196in)
Bucket Dia.: 0.45 mm (0.0177in)
Max. Solid Conductor: 0.12 mm² (AWG 28)
Max. Stranded Conductor: 0.12 mm² (AWG 28)
R (max): 8.5 mOhm
Test voltage (kV rms) Contact-contact: 0.60
Air clearance min.: 0.48 mm

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.


Creepage distance min.: 0.48 mm

Others

Endurance (Shell): >2000 mating cycles

Temp (min / max): -50°C / +170°C

DRAWINGS



Dimensions

| | A | L |
|-----|------|------|
| mm. | 15.5 | 48 |
| in. | 0,61 | 1,89 |

RECOMMENDED BY LEMO

Tools

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[LEMO:](#)

[SAN.M22.GLA.7AZ](#)