

SUMMARY

Wires

Low voltage 22

Image is for illustrative purpose only

Series SP
Termination type Male print PCB
IP rating 50
AWG wire size 36.00 - 28.00
Cable Ø 0.00 - 0.00 mm
Status active

Download

[Request a quote](#)

[Catalog](#)

TECHNICAL DETAILS

Mechanics

Shell Style/Model *:
Keying 3 keys (alpha=0, gamma=50, plug: female contacts, receptacle: male contacts)
Housing Material Proprietary sulfone, black
Variant N : Black front nut
Weight 24.63 g

Performance

Configuration SP.M22 : 22 Low V.
Insulator L: PEEK (UL 94 / V-0/1.5)
Rated Current

Specifications

Contact Type: Print (straight)
Contact Dia.: 0.5 mm (0.0196in)
R (max): 8.5 mOhm

Others

Endurance (Shell): >2000 mating cycles

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Temp (min / max): -50°C / +170°C

DRAWINGS



RECOMMENDED BY LEMO

Tools

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[LEMO:](#)

[SKS.M22.NLDN](#)