



LEOPARD
IMAGING

LI-IMX728RCCB-GM2B-120H-DSL



Address:

910 Auburn Ct
Fremont, CA 94538
USA



Phone:

+1 (408)263-0988

Fax:

+1 (408)217-1960



Sales:

sales@leopardimaging.com

Support:

support@leopardimaging.com

INTRODUCTION

The LI-IMX728RCCB-GM2B-120H-DSL is equipped with Sony diagonal 9.30 mm 8.39MP CMOS RCCB sensor IMX728 and Maxim GMSL2 serializer MAX96717. This camera outputs RAW image data.

SPECIFICATIONS

Sensor	Diagonal 9.30 mm 8.39MP CMOS RCCB Sensor IMX728 (ES3 version)
Optical Format	1/1.72"
Resolution	3857 (H) x 2177 (V) (active pixels)
Pixel Size	2.1 x 2.1 μ m
Color / Mono	Color sensor
Output Format	20-bit / 16-bit / 12-bit / 10-bit RAW data
Frame Rate	30 fps @ 3856 x 2176
HDR (High Dynamic Range)	Supported
LFM (LED Flicker Mitigation)	Supported
Serializer	Maxim MAX96717G
Power Supply Range	9 ~ 19 VDC
Connector	FAKRA Z TYPE
Waterproof	No
Power Consumption	Approx. 121 mA @ 12 VDC (3856 x 2176 @ 15 fps)
Operating Temp	-40°C ~ +85°C
Storage Temp	-40°C ~ +85°C
Weight	~ 43 g
Part#	LI-IMX728RCCB-GM2B-120H-DSL

APPLICATIONS

- Automotive
 - ◆ High Resolution Front Viewing
 - ◆ Machine Vision
 - ◆ Autonomous Driving
 - ◆ Assisted Driving
 - ◆ Digital Video Recording

IMAGE ORIENTATION




LENS SPECIFICATIONS


Focal Length	5.1 mm $\pm$ 2%
Aperture, F/#	1.6 $\pm$ 5%
Field of View (FOV)	120° horizontal
IR Cut Filter	700 nm IR cut filter
Lens Mount	M16 x P0.5



DIMENSIONS



PINOUT CONNECTIONS




USB3.0 CAMERA KIT

LI-GMSL2-USB



Top View



Bottom View

LI-IMX728RCCB-GM2B-120H-DSL can connect to LI-GMSL2-USB as a USB 3.0 camera.

Part#: **LI-USB30-IMX728RCCB-GM2B-120H-DSL**

SPECIFICATIONS

- USB 3.0 Super Speed support
- UVC compliant
- Allows customization
- 12 VDC Power Supply for camera
- Weight: ~ 110 g
- Single Coax Cable transmits up to 12 meters PoC (Power over Cable)
- Resolution: 3856 x 2176 @ 15 fps
- Power consumption: Approx. 121 mA @ 12 VDC
- Compatible with Windows, Linux OS and other OS which have UVC drivers

BOM

#	Items	QTY
1	LI-IMX728RCCB-GM2B-120H-DSL	1
2	LI-GMSL2-USB	1
3	3-Meter Fakra Cable	1
4	12 VDC Power Supply	1
5	USB3.0 Cable	1



SDK SUPPORTED

- Camera Tool Source Code in C#
- Capture & Display
- Register Access Function

- REVISION HISTORY

Revision	Description	Release Date
0.1	Initial draft.	13 Jul 2023
0.2	Updated image direction.	27 Dec 2023

910 Auburn Ct, Fremont, CA 94538, USA
Phone: +1-408-263-0988
Fax: +1-408-217-1960
Email: sales@leopardimaging.com
Website: www.leopardimaging.com



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Leopard Imaging:](#)

[LI-IMX728RCCB-GM2B-120H-DSL](#) [LI-USB30-IMX728RCCB-GM2B-120H-DSL](#)