








VIEW: M
SCALL:3:1


- * 1. 端子平面度小于0.08 mm。
2. 每卷包装数量为2000pcs。

[illegible]

注:每档至接通范围约36°



Circuit Diagram



P.C.B Land dimension

规格 Specifications

额定负荷 Ratings	DC 5V 10mA
初期接触电阻 Initial Contact Resistance	200mΩ Max.
绝缘电阻 Insulation Resistance	DC 100V 60±5Sec. 250MΩ Min.
抗电强度 Dielectric Voltage	AC 250V(50~60Hz) 60 Sec.
扭力 Operating Force	90±15 gf.cm
负荷寿命 Operating Life With Load	7,000次 (+360° or -360° is 1 cycles)
接触行程 Pre Travel	36°(旋转)
回路 Poles-Throws	1P1OT

专利产品 Patent

6	接触片 CONTACT	C1720	1	Au PLATED
5	弹片 SPRING PLATE	SUS	2	NATURAL
4	端子 TERMINAL	C5210R	1	Ag PLATED
3	胶壳 HOUSING	LCP	1	BLACK C
2	盖片 COVER	SUS	1	Ag PLATED
1	旋钮 ROTARY KNOB	PA	1	BLACK C
序NO.	零件 PART	材料 MATERIAL	数量 QTY	备注 REMARKS

标号 REV	内容 DESCRIPTION	签名 SIGN.	日期 DATE
DWG NO. ITEM3056			

TOLERANCES UNLESS OTHERWISE SPEC.		TITLE	ROTARY SWITCH		ITEM NO	RW-1106-NS RT		
UNDER 1	± 0.10	DRAWN	廖铁军	2008-12-19	VERSION	A01	PAGE 1	OF 1
1 - 10	± 0.30	REVIEWED	方 勇	2008-12-19	SCALE		UNIT	mm
OVER 10	± 0.50	APPROVED	程先金	2008-12-19	PROJECTION			

COMAX

高铭电子（惠州）有限公司
Comax Electronics(Huizhou)Co.,Ltd.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[C&K Switches:](#)

[RW1106NSRT](#) [RW-1106-NS RT](#)