

# WSP 80

Product no.: T0052916199N



## Benefits

- › Soldering Iron 80 W, 24 V with knurled nut for fast tip exchange
- › For medium components with high energy demand
- › For universal soldering jobs with WT stations and WR rework stations
- › Extensive range of LT soldering tips
- › Silver-Line heating technology
- › Fast heating up



### Technical Data

|   |  |
|---|--|
| Active Tip heating element technology     | ---  |
| Power Response heating element technology | ---  |
| Silver Line heating element technology    | on   |
| Voltage                                   | 24 V   |
| Power                                     | 80 W   |
| Tip range                                 | LT   |
| Supply unit                               | PU 81, PUD 81, PUD 81i, PU WAD 101, PUD 121, PU WAD 101IG, PUD 151, WD 1, WD 1M, WR 2, WR 3M, WR 3ME, WT 1, WT 1H, WT 2M |
| WX-compatible                             | ---  |
| Temperature range °C                      | 50 - 450   |
| Temperature range °F                      | 150 - 850  |
| Heating time                              | 10   |
| Safety rest                               | ---  |
| Safety rest (optional)                    | KH 18 (T0051517099), WDH 10 (T0051512199), WDH 10T (T0051516199)   |
| Barrel                                    | T0058744710  |
| Integrated direct extraction              | Attachment T0052918699 / T0052918599   |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Apex Tool Group:](#)

[WSP80](#)