

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0015247180](#)
Status: **Active**
Overview: [Mini-Fit Family Power Connectors](#)
Description: Mini-Fit BMI Receptacle Header, 4.20mm Pitch, Dual Row, Vertical, with Snap-In Plastic Pegs, Post 2.54µm Tin (Sn), UL 94V-2, 18 Circuits

Documents:

3D Model (PDF)	Product Specification PS-5556-002-001 (PDF)
3D Model	Packaging Specification PK-42385-999-001 (PDF)
Drawing (PDF)	Test Summary 423850000-TS-000 (PDF)
Product Specification 55560002-PS-CH-000 (PDF)	Test Summary TS-5556-002-001 (PDF)
Product Specification 55560002-PS-ES-000 (PDF)	Symbol Footprint Data SYM-A42385-18XX-001 (PDF)
Product Specification 55560002-PS-SK-000 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	PCB Receptacles
Series	42385
Application	Board-to-Board, Power, Wire-to-Board
Comments	Solder Type With Pegs
Overview	Mini-Fit Family Power Connectors
Product Name	Mini-Fit BMI
UPC	800754209526

Physical

Circuits (Loaded)	18
Circuits (maximum)	18
Color - Resin	Natural
Durability (mating cycles max)	30
Flammability	94V-2
Glow-Wire Capable	No
Guide to Mating Part	Yes
Keying to Mating Part	None
Lock to Mating Part	None
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Resin	Nylon
Net Weight	3.665/g
Number of Rows	2
Orientation	Vertical
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.20mm
Packaging Type	Tray
Pitch - Mating Interface	4.20mm
Pitch - Termination Interface	4.20mm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Through Hole

Electrical

Current - Maximum per Contact	9.0A
-------------------------------	------



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[42385 Series](#)

Mates With

Panel Mount Plug [42475](#)
Right Angle
Headers [42404](#) , [43810](#)
Vertical
Headers [42440](#) , [43879](#) , [44068](#)

Grounding to PCB No
Voltage - Maximum 600V AC (RMS)/DC

Solder Process Data

Duration at Max. Process Temperature (seconds) 005
Lead-free Process Capability WAVE
Max. Cycles at Max. Process Temperature 001
Process Temperature max. C 240

Material Info

Engineering Number 42385-18A1

Reference - Drawing Numbers

Packaging Specification PK-42385-999-001
Product Specification 55560002-PS-CH-000, 55560002-PS-ES-000,
55560002-PS-SK-000, PS-5556-002-001
Sales Drawing SDA-42385-X-001
Symbol/Footprint Data SYM-A42385-18XX-001
Test Summary 423850000-TS-000, TS-5556-002-001

This document was generated on 12/14/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[15-24-7180](#)