

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [002211121](#)
Status: **Active**
Overview: [Mini-Latch Wire-to-Board / Wire-to-Wire Connector System](#)
Description: Mini-Latch / KK Wire-to-Board Header, Vertical, with Friction Ramp, 12 Circuits, Gold (Au) Plating, Natural

Documents:

3D Model	Application Specification 511910000-AS-000 (PDF)
Drawing (PDF)	Application Specification 511910000-AS-001 (PDF)
Product Specification 50510002-PS-000 (PDF)	Packaging Specification SPK-5045-002-001 (PDF)
Product Specification PS-5045-003 (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-5045-004 (PDF)	

Agency Certification


UL E29179

General

Product Family	PCB Headers
Series	5045
3D Viewer	Yes
Application	Signal, Wire-to-Board
CURRENT-MAX-NUMERIC	3.0
Overview	Mini-Latch Wire-to-Board / Wire-to-Wire Connector System
PITCH-MATING-NUMERIC	2.50
Product Name	KK, Mini-Latch
UPC	800753732827

Physical

Breakaway	No
Circuits (Loaded)	12
Circuits (maximum)	12
Color - Resin	Natural
Durability (mating cycles max)	30
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Material - Resin	Polyamide
Net Weight	1198.000/mg
Number of Rows	1
Orientation	Vertical
PC Tail Length	3.40mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.60mm
Packaging Type	Bag
Pitch - Mating Interface	2.50mm
Pitch - Termination Interface	2.50mm
Plating min - Mating	0.356µm
Plating min - Termination	0.356µm
Polarized to PCB	No



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/88/2018 (15
January 2019)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[5045 Series](#)

Mates With

2.50mm Pitch Housings [51191](#) , [5051](#)

Shrouded	Partial
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Through Hole

Electrical

Current - Maximum per Contact	3.0A
Voltage - Maximum	250V

Material Info

Engineering Number	5045-12AG
--------------------	-----------

Reference - Drawing Numbers

Application Specification	511910000-AS-000, 511910000-AS-001
Packaging Specification	SPK-5045-002-001
Product Specification	50510002-PS-000, PS-5045-003, PS-5045-004
Sales Drawing	SD-5045-001-001

This document was generated on 07/26/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[22-11-1121](#)