

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0022232281](#)
Status: **Active**
Overview: [KK Interconnect Solutions](#)
Description: KK 254 Solid Header, Vertical, with Friction Lock, 28 Circuits, Tin (Sn) Plating

Documents:

| | |
|--|--|
| 3D Model | Packaging Specification PK-6373-001-000 (PDF) |
| Drawing (PDF) | Symbol Footprint Data SYM-22-23-2281-001 (PDF) |
| 3D Model (PDF) | RoHS Certificate of Compliance (PDF) |
| Product Specification PS-10-07-001 (PDF) | |

Agency Certification

| | |
|-----|---------|
| CSA | LR19980 |
| UL | E29179 |

General

| | |
|----------------|---|
| Product Family | PCB Headers |
| Series | 6373 |
| Application | Signal, Wire-to-Board |
| Overview | KK Interconnect Solutions |
| Product Name | KK 254 |
| UPC | 800754934398 |

Physical

| | |
|--------------------------------|---------------------------|
| Breakaway | No |
| Circuits (Loaded) | 28 |
| Circuits (maximum) | 28 |
| Color - Resin | Natural (White) |
| Durability (mating cycles max) | 25 |
| First Mate / Last Break | No |
| Flammability | 94V-0 |
| Glow-Wire Capable | No |
| Guide to Mating Part | No |
| Lock to Mating Part | Yes |
| Material - Metal | Brass |
| Material - Plating Mating | Tin |
| Material - Resin | Nylon |
| Net Weight | 3.273/g |
| Number of Rows | 1 |
| Orientation | Vertical |
| PC Tail Length | 3.56mm |
| PCB Locator | No |
| PCB Retention | None |
| PCB Thickness - Recommended | 1.60mm |
| Packaging Type | Bag |
| Pitch - Mating Interface | 2.54mm |
| Pitch - Termination Interface | 2.54mm |
| Polarized to Mating Part | Yes |
| Polarized to PCB | No |
| Shrouded | Partial |
| Stackable | No |
| Temperature Range - Operating | See Product Specification |
| Termination Interface: Style | Through Hole |

Electrical

| | |
|-------------------------------|------|
| Current - Maximum per Contact | 4.0A |
| Voltage - Maximum | 500V |



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[6373 Series](#)

Mates With

[2695](#) , [6471](#) , [7880](#) , [4455](#) , [7720](#)

Solder Process Data

| | |
|--|------|
| Duration at Max. Process Temperature (seconds) | 005 |
| Lead-free Process Capability | WAVE |
| Max. Cycles at Max. Process Temperature | 001 |
| Process Temperature max. C | 235 |

Material Info

| | |
|--------------------|---------------|
| Engineering Number | A-6373-28A222 |
|--------------------|---------------|

Reference - Drawing Numbers

| | |
|-------------------------|----------------------------------|
| Packaging Specification | PK-6373-001-000 |
| Product Specification | PS-10-07-001 |
| Sales Drawing | SD-6373-001-000, SD-6373-001-002 |
| Symbol/Footprint Data | SYM-22-23-2281-001 |

This document was generated on 09/13/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[22-23-2281](#)