

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0150200095**
Status: **Active**
Overview: FFC Cable Jumpers, Premo-Flex Flat-Flexible Cable Jumpers
Description: 0.50mm Pitch Premo-Flex FFC Jumper, Same Side Contacts (Type A), 30.00mm Cable Length, Gold (Au) Plating, 10 Circuits

Documents:

[Drawing \(PDF\)](#) [Datasheet \(PDF\)](#)
[Product Specification PS-15020-001-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family Cable
Series 15020
Comments Contacts on the same side, Type A
Crimp Quality Equipment Yes
Overview [FFC Cable Jumpers, Premo-Flex Flat-Flexible Cable Jumpers](#)
Product Name Premo-Flex FFC Jumper
UPC 884982175570

Physical

Cable Length 30.00mm
Circuits (Loaded) 10
Contact Layout Type A (same side)
Material - Plating Mating Gold
Net Weight 0.363/g
Packaging Type Bag
Pitch - Mating Interface 0.50mm
Temperature Range - Operating -40° to +105°C
Wire Size AWG N/A
Wire/Cable Type Flat Flex Cable

Electrical

Current - Maximum per Contact 0.5A
Voltage - Maximum 60V AC

Material Info

Reference - Drawing Numbers

Product Specification PS-15020-001-001
Sales Drawing SD-15020-001-001



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

15020 Series

Mates With

Easy-On FFC/FPC Connector:

[5034801000](#) , [5051101092](#) , [527451097](#) ,
[527461071](#) , [5019511030](#) , [5019511050](#) ,
[525591052](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[15020-0095](#)