

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0150200342](#)  
**Status:** **Active**  
**Overview:** FFC Cable Jumpers, Premo-Flex Flat-Flexible Cable Jumpers  
**Description:** 0.50mm Pitch Premo-Flex FFC Jumper, Opposite Side Contacts (Type D), 76.00mm Cable Length, Gold (Au) Plating, 32 Circuits

**Documents:**

[Drawing \(PDF\)](#) [Datasheet \(PDF\)](#)  
[Product Specification PS-15020-001-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family Cable  
 Series [15020](#)  
 Comments Contacts on opposite sides, Type D  
 Crimp Quality Equipment Yes  
 Overview [FFC Cable Jumpers, Premo-Flex Flat-Flexible Cable Jumpers](#)  
 Product Name Premo-Flex FFC Jumper  
 UPC 884982178045

**Physical**

Cable Length 76.00mm  
 Circuits (Loaded) 32  
 Contact Layout Type D (opposite side)  
 Material - Plating Mating Gold  
 Net Weight 0.816/g  
 Packaging Type Bag  
 Pitch - Mating Interface 0.50mm  
 Temperature Range - Operating -40° to +105°C  
 Wire Size AWG N/A  
 Wire/Cable Type Flat Flex Cable

**Electrical**

Current - Maximum per Contact 0.5A  
 Voltage - Maximum 60V AC

**Material Info**

**Reference - Drawing Numbers**

Product Specification PS-15020-001-001  
 Sales Drawing SD-15020-001-001



**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[15020 Series](#)

**Mates With**

Easy-On FFC/FPC Connector: <br>  
[5034803200](#) , [5051103291](#) , [5051103296](#)  
 , [541043231](#) , [541323262](#) , [5019513210](#) ,  
[5019513230](#) , [5019513250](#) , [525593252](#)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[15020-0342](#)