

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0150200875**
Status: **Active**
Overview: FFC Cable Jumpers, Premo-Flex Flat-Flexible Cable Jumpers
Description: 0.50mm Pitch Premo-Flex FFC Jumper, Same Side Contacts (Type A), 305.00mm Cable Length, Gold (Au) Plating, 17 Circuits

Documents:

[Drawing \(PDF\)](#) [Datasheet \(PDF\)](#)
[Product Specification PS-15020-001-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family Cable
 Series 15020
 Comments Contacts on the same side, Type A
 Crimp Quality Equipment Yes
 Overview FFC Cable Jumpers, Premo-Flex Flat-Flexible Cable Jumpers
 Product Name Premo-Flex FFC Jumper
 UPC 884982181502

Physical

Cable Length 305.00mm
 Circuits (Loaded) 17
 Contact Layout Type A (same side)
 Material - Plating Mating Gold
 Packaging Type Bag
 Pitch - Mating Interface 0.50mm
 Temperature Range - Operating -40° to +105°C
 Wire Size AWG N/A
 Wire/Cable Type Flat Flex Cable

Electrical

Current - Maximum per Contact 0.5A
 Voltage - Maximum 60V AC

Material Info

Reference - Drawing Numbers

Product Specification PS-15020-001-001
 Sales Drawing SD-15020-001-001



EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

15020 Series

Mates With

Easy-On FFC/FPC Connector:

[5034801700](#) , [5051101792](#) , [527451797](#) ,
[527461771](#) , [5019511730](#) , [5019511750](#) ,
[525591752](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[15020-0875](#)