

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **0151660555**  
**Status:** **Active**  
**Overview:** FFC Cable Jumpers, Premo-Flex Flat-Flexible Cable Jumpers  
**Description:** 0.50mm Pitch Premo-Flex FFC Jumper, Same Side Contacts (Type A), 305.00mm Cable Length, Tin (Sn) Plating, 50 Circuits

**Documents:**

[Drawing \(PDF\)](#) [Datasheet \(PDF\)](#)  
[Product Specification PS-15166-001-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**General**

|                         |   |
|-------------------------|---|
| Product Family          | Cable   |
| Series                  | 15166   |
| Comments                | Contacts on the same side, Type A   |
| Crimp Quality Equipment | Yes   |
| Overview                | <a href="#">FFC Cable Jumpers, Premo-Flex Flat-Flexible Cable Jumpers</a> |
| Product Name            | Premo-Flex FFC Jumper   |
| UPC                     | 884982850538  |

**Physical**

|                               |                 |
|-------------------------------|-----------------|
| Cable Length                  | 305.00mm        |
| Circuits (Loaded)             | 50              |
| Contact Layout Type           | A (same side)   |
| Material - Plating Mating     | Tin             |
| Net Weight                    | 1.000/g         |
| Packaging Type                | Bag             |
| Pitch - Mating Interface      | 0.50mm          |
| Temperature Range - Operating | -40° to +105°C  |
| Wire Size AWG                 | N/A             |
| Wire/Cable Type               | Flat Flex Cable |


**Electrical**

|                               |        |
|-------------------------------|--------|
| Current - Maximum per Contact | 0.5A   |
| Voltage - Maximum             | 60V AC |

**Material Info**

**Reference - Drawing Numbers**

|                       |                  |
|-----------------------|------------------|
| Product Specification | PS-15166-001-001 |
| Sales Drawing         | SD-15166-001-001 |



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

15166 Series

**Mates With**

Easy-On FFC/FPC Connector: . [541045033](#)  
, [541325033](#) , [5019515000](#)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[15166-0555](#)