

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0152670569](#)
Status: **Active**
Overview:
Description: 1.00mm Pitch Premo-Flex FFC Jumper, Same Side Contacts (Type A), 229.00mm Cable Length, Tin (Sn) Plating, 38 Circuits

General

Product Family	Cable
Series	15267
Comments	Contacts on the same side, Type A
Crimp Quality Equipment	Yes
Overview	premo-flex
Product Name	Premo-Flex FFC Jumper
UPC	884982448216

Physical

Cable Length	229.00mm
Circuits (Loaded)	38
Contact Layout Type	A (same side)
Material - Plating Mating	Tin
Net Weight	6.359/g
Packaging Type	Bag
Pitch - Mating Interface	1.00mm
Temperature Range - Operating	-40° to +105°C
Wire Size AWG	N/A
Wire/Cable Type	Flat Flex Cable

Electrical

Current - Maximum per Contact	1.2A
Voltage - Maximum	60V AC

Material Info

Reference - Drawing Numbers

Product Specification	PS-15267-001-001
Sales Drawing	SD-15267-001-001

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[15267](#) Series

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[15267-0569](#)