

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0152670574](#)  
**Status:** **Active**  
**Overview:** FFC Cable Jumpers, Premo-Flex Flat-Flexible Cable Jumpers  
**Description:** 1.00mm Pitch Premo-Flex FFC Jumper, Opposite Side Contacts (Type D), 305.00mm Cable Length, Tin (Sn) Plating, 38 Circuits

**Documents:**

<a href="#">Drawing (PDF)</a>	<a href="#">Datasheet (PDF)</a>
<a href="#">Product Specification PS-15267-001-001 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>

**General**

Product Family	Cable
Series	<a href="#">15267</a>
Comments	Contacts on opposite sides, Type D
Crimp Quality Equipment	Yes
Overview	<a href="#">FFC Cable Jumpers, Premo-Flex Flat-Flexible Cable Jumpers</a>
Product Name	Premo-Flex FFC Jumper
UPC	884982448360

**Physical**

Cable Length	305.00mm
Circuits (Loaded)	38
Contact Layout Type	D (opposite side)
Material - Plating Mating	Tin
Net Weight	8.429/g
Packaging Type	Bag
Pitch - Mating Interface	1.00mm
Temperature Range - Operating	-40° to +105°C
Wire Size AWG	N/A
Wire/Cable Type	Flat Flex Cable

**Electrical**

Current - Maximum per Contact	1.2A
Voltage - Maximum	60V AC

**Material Info**

**Reference - Drawing Numbers**

Product Specification	PS-15267-001-001
Sales Drawing	SD-15267-001-001



*Series image - Reference only*

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[15267 Series](#)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[15267-0574](#)