

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0152670719](#)  
**Status:** **Active**  
**Overview:** FFC Cable Jumpers, Premo-Flex Flat-Flexible Cable Jumpers  
**Description:** 1.00mm Pitch Premo-Flex FFC Jumper, Same Side Contacts (Type A), 254.00mm Cable Length, Tin (Sn) Plating, 4 Circuits

**Documents:**

|  |  |
|--|--|
| <a href="#">Drawing (PDF)</a>                                | <a href="#">Datasheet (PDF)</a>                      |
| <a href="#">Product Specification PS-15267-001-001 (PDF)</a> | <a href="#">RoHS Certificate of Compliance (PDF)</a> |

**General**

|                         |   |
|-------------------------|---|
| Product Family          | Cable   |
| Series                  | <a href="#">15267</a>   |
| Comments                | Contacts on the same side, Type A   |
| Crimp Quality Equipment | Yes   |
| Overview                | <a href="#">FFC Cable Jumpers, Premo-Flex Flat-Flexible Cable Jumpers</a> |
| Product Name            | Premo-Flex FFC Jumper   |
| UPC                     | 884982449633  |

**Physical**

|                               |                 |
|-------------------------------|-----------------|
| Cable Length                  | 254.00mm        |
| Circuits (Loaded)             | 4               |
| Contact Layout Type           | A (same side)   |
| Material - Plating Mating     | Tin             |
| Packaging Type                | Bag             |
| Pitch - Mating Interface      | 1.00mm          |
| Temperature Range - Operating | -40° to +105°C  |
| Wire Size AWG                 | N/A             |
| Wire/Cable Type               | Flat Flex Cable |

**Electrical**

|                               |        |
|-------------------------------|--------|
| Current - Maximum per Contact | 1.2A   |
| Voltage - Maximum             | 60V AC |

**Material Info**

**Reference - Drawing Numbers**

|                       |                  |
|-----------------------|------------------|
| Product Specification | PS-15267-001-001 |
| Sales Drawing         | SD-15267-001-001 |



*Series image - Reference only*

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[15267 Series](#)

**Mates With**

Easy-On FFC/FPC Connector: <br>[522070433](#) , [522710479](#)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[15267-0719](#)