

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0152681100**
Status: **Active**
Overview: FFC Cable Jumpers, Premo-Flex Flat-Flexible Cable Jumpers
Description: 1.25mm Pitch Premo-Flex FFC Jumper, Opposite Side Contacts (Type D), 76.00mm Cable Length, Tin (Sn) Plating, 39 Circuits

Documents:

[Drawing \(PDF\)](#) [Datasheet \(PDF\)](#)
[Product Specification PS-15268-001-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family Cable
Series [15268](#)
Comments Contacts on opposite sides, Type D
Crimp Quality Equipment Yes
Overview [FFC Cable Jumpers, Premo-Flex Flat-Flexible Cable Jumpers](#)
Product Name Premo-Flex FFC Jumper
UPC 884982424685

Physical

Cable Length 76.00mm
Circuits (Loaded) 39
Contact Layout Type D (opposite side)
Material - Plating Mating Tin
Packaging Type Bag
Pitch - Mating Interface 1.25mm
Temperature Range - Operating -40° to +105°C
Wire Size AWG N/A
Wire/Cable Type Flat Flex Cable

Electrical

Current - Maximum per Contact 1.4A
Voltage - Maximum 60V AC

Material Info

Reference - Drawing Numbers

Product Specification PS-15268-001-001
Sales Drawing SD-15268-001-001



EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[15268 Series](#)

Mates With

Molex FFC – FPC connector. Be sure to match like plating.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[15268-1100](#)