


**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0190270111](#)  
**Status:** **Active**  
**Overview:** [Application Tooling](#)  
**Description:** ATP Crimp Dies for VersaKrimp Copper Ring Tongue Terminals And Butt Splices on Tape, 8 AWG

**Documents:**  
[RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Application Tooling
Series	207126
Comments	The Crimp Tape Module <a href="#">640162000</a> is a base unit that will work like an applicator in a Molex TM-3000 <a href="#">638017200</a> , <a href="#">638017300</a> industry standard crimp press or the Molex TM-4000 <a href="#">638017600</a> industry standard crimp press. The Crimp Tape Module will accept all ATP-301 and ATP-201 style crimp dies. This Crimp Tape Module will allow customers to process most of Molex's Mylar Tape product from 2 AWG uninsulated and 4 AWG insulated products and up. The Crimp Tape Module will NOT work in any other industry standard crimp press or wire process machine. These ATP-301 style die sets can be used in the older style suitcase presses.
Function	Crimp
Geographic Area	Global
Level of Automation	Semi-Automatic
More Detailed Tech Information	<a href="mailto:applicationtooling@molex.com">applicationtooling@molex.com</a>
Overview	<a href="#">Application Tooling</a>
Product Name	ETC, VersaKrimp
Tool Type	Crimp Module
UPC	800753041165
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.
<b>Physical</b>	
Net Weight	48.990/g
<b>Material Info</b>	
Engineering Number	ATP-D-141
<b>Reference - Drawing Numbers</b>	
Application Tooling Documents	ATS-190270111-001, TM-192280498-001, TM-640160065-001, TM-640160065CN-001, TM-640160065DE-001, TM-640160065FR-001, TM-640160065IT-001, TM-640160065JP-001,



**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

207126 Series

**Use With**

Molex Crimp Tape Module [640162000](#) used with Molex TM-3000: [638017200](#) , [638017300](#) , Molex TM-4000: [638017600](#) , Molex ATP-301 Press: [192280030](#) and Molex ATP-101 style presses.

**Application Tooling** | **FAQ**

**Description** | **Product #**

VersaKrimp Ring Tongue Terminal for 8 AWG Wire, Stud Size 8 (M4), Mylar Tape Carrier	<a href="#">191930148</a>
VersaKrimp Ring Tongue Terminal for 8 AWG Wire, Stud Size 10 (M5), Mylar Tape Carrier	<a href="#">191930151</a>
VersaKrimp Ring Tongue Terminal for 8 AWG Wire, Stud Size 1/4" (M6), Mylar Tape Carrier	<a href="#">191930155</a>

TM-640160065KR-001, TM-640160065MY-001,  
TM-640160065PL-001, TM-640160065RU-001,  
TM-640160065SK-001, TM-640160065SP-001,  
TM-640160065TH-001, TM-640160065TW-001,  
TM-640160065VN-001

VersaKrimp Ring 191930158  
Tongue Terminal  
for 8 AWG Wire,  
Stud Size 5/16" (M8),  
Mylar Tape Carrier  
D-351-38T RING 191930170  
VERSAKRIMP TAPE  
DBL SPACE

This document was generated on 10/07/2021

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19027-0111](#)