

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0190270133](#)  
**Status:** **Active**  
**Overview:** [Application Tooling](#)  
**Description:** Perishable Tooling Spacers for tape product

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Application Tooling
Series	<a href="#">207126</a>
Comments	Spacer (Lower) 190270200, Spacer (Upper) 190270201
Function	Crimp
Geographic Area	Global
Level of Automation	Semi-Automatic
More Detailed Tech Information	<a href="mailto:applicationtooling@molex.com">applicationtooling@molex.com</a>
Overview	<a href="#">Application Tooling</a>
Product Name	ETC
Tool Type	Crimp Module
UPC	800753041233
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

**Material Info**

Engineering Number ATP-DS-187

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[207126 Series](#)

**Use With**

Perishable Tool Kit

**Application Tooling**

**Description**

**FAQ**

**Product #**

Krimptite Ring Tongue Terminal for 18-22 AWG Wire	<a href="#">190690050</a>
Krimptite Ring Tongue Terminal for 14-16 AWG Wire	<a href="#">190690094</a>
Krimptite Ring Tongue Terminal for 14-16 AWG Wire	<a href="#">190690097</a>
Krimptite Ring Tongue Terminal for 10-12 AWG Wire, Stud Size 1/4" (M6), Length 26.82mm, Mylar Tape Carrier	<a href="#">190690240</a>
Krimptite Ring Tongue Terminal for 10-12 AWG Wire, Stud Size 3/8" (M9), Length 26.82mm, Mylar Tape Carrier	<a href="#">190690243</a>
Krimptite Ring Tongue Terminal for 10-12 AWG Wire, Stud Size 5/16" (M8), Length 26.82mm, Mylar Tape Carrier	<a href="#">190690246</a>
InsulKrimp Ring Tongue Terminal for 18-22 AWG Wire	<a href="#">190700035</a>

InsulKrimp Ring	<u>190700039</u>
Tongue Terminal for 18-22 AWG Wire	
InsulKrimp Ring	<u>190700061</u>
Tongue Terminal for 14-16 AWG Wire	
InsulKrimp Ring	<u>190700064</u>
Tongue Terminal for 14-16 AWG Wire	
InsulKrimp Ring	<u>190700151</u>
Tongue Terminal for 10-12 AWG Wire, Stud Size 1/4" (M6), Length 34.21mm, Mylar Tape Carrier	
InsulKrimp Ring	<u>190700154</u>
Tongue Terminal for 10-12 AWG Wire, Stud Size 3/8" (M9), Length 34.21mm, Mylar Tape Carrier	
InsulKrimp Ring	<u>190700156</u>
Tongue Terminal for 10-12 AWG Wire, Stud Size 5/16" (M8), Length 34.21mm, Mylar Tape Carrier	
Avikrimp Ring	<u>190730060</u>
Tongue Terminal for 14 to 16 AWG Wire, Stud Size 3/8" (M9), Length 31.12mm, Mylar Tape Carrier	
Avikrimp Ring	<u>190730062</u>
Tongue Terminal for 14 to 16 AWG Wire, Stud Size 5/16" (M8), Length 31.12mm, Mylar Tape Carrier	
Avikrimp Ring	<u>190730232</u>
Tongue Terminal for 10 to 12 AWG Wire, Stud Size 1/4" (M6), Length 34.59mm, Mylar Tape Carrier	
Avikrimp Ring	<u>190730234</u>
Tongue Terminal for 10 to 12 AWG Wire, Stud Size 1/4" (M6), Expanded Flare, Length 34.59mm, Mylar Tape Carrier	
Avikrimp Ring	<u>190730237</u>
Tongue Terminal for 10 to 12 AWG Wire, Stud Size 3/8" (M9), Length 34.59mm, Mylar Tape Carrier	
Avikrimp Ring	<u>190730239</u>
Tongue Terminal for 10 to 12 AWG Wire, Stud Size 3/8" (M9), Expanded Flare, Length 34.59mm, Mylar Tape Carrier	

This document was generated on 07/29/2021

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19027-0133](#)