

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0190270135](#)
Status: **Active**
Overview: [Application Tooling](#)
Description: Perishable Tooling Spacers for tape product

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Application Tooling
Series	207126
Comments	Spacer (Lower) 190270204, Spacer (Upper) 190270205
Function	Crimp
Geographic Area	Global
Level of Automation	Semi-Automatic
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	ETC
Tool Type	Crimp Module
UPC	800753041264
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info

Engineering Number ATP-DS-350

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[207126](#) Series

Use With

Perishable Tool Kit

Application Tooling

Description

FAQ

Product #

Krimptite Ring Tongue Terminal for 14-16 Heavy Duty AWG Wire	190440138
Krimptite Ring Tongue Terminal for 10-12 AWG Wire, Stud Size 7/16" (M11), Length 32.51mm, Mylar Tape Carrier	190690146
InsulKrimp Ring Tongue Terminal for 10-12 AWG Wire, Stud Size 1/2" (M12), Length 39.90mm, Mylar Tape Carrier	190700110
InsulKrimp Ring Tongue Terminal for 10-12 AWG Wire, Stud Size 7/16" (M11), Length 39.90mm, Mylar Tape Carrier	190700116
Avikrimp Ring Tongue Terminal for 10 to 12 AWG Wire, Stud Size 1/2" (M12), Length 40.13mm, Mylar Tape Carrier	190730146

C-301-12T RING	<u>191930095</u>
KRIMPTITE TAPE	
DBL SPACE	
C-301-76T RING	<u>191930100</u>
VERSAKRIMP TAPE	
DBL SPACE	

This document was generated on 07/31/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19027-0135](#)