

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0190730173**
Status: **Active**
Overview: Solderless Terminals
Description: Avikrimp Ring Tongue Terminal for 10 to 12 AWG Wire, Stud Size 10 (M5), Expanded Flare, Length 27.71mm

Documents:

| | |
|--------------------------------|--|
| 3D Model | Product Specification PS-19902-011-001 (PDF) |
| Drawing (PDF) | Product Specification PS-19902-013-001 (PDF) |
| 3D Model (PDF) | RoHS Certificate of Compliance (PDF) |

Agency Certification

| | |
|-----|---------|
| CSA | LR18689 |
| UL | E32244 |

General

| | |
|-------------------------|-----------------------------|
| Product Family | Ring and Spade Terminals |
| Series | <u>19073</u> |
| Crimp Quality Equipment | Yes |
| Overview | <u>Solderless Terminals</u> |
| Product Name | Avikrimp |
| Type | Ring |
| UPC | 800753077089 |

Physical

| | |
|---------------------------|-------------|
| Barrel Type | Closed |
| Flammability | 94V-2 |
| Insulation | Nylon (PA) |
| Material - Plating Mating | Tin |
| Net Weight | 2.191/g |
| Packaging Type | Bag |
| Stud Size | 10 (M5) |
| Wire Insulation Diameter | 6.35mm max. |
| Wire Size AWG | 10, 12 |
| Wire Size mm ² | 4.00-6.00 |

Solder Process Data

| | |
|------------------------------|-----|
| Lead-free Process Capability | N/A |
|------------------------------|-----|

Material Info

| | |
|--------------------|-----------|
| Engineering Number | C-828-10X |
|--------------------|-----------|

Reference - Drawing Numbers

| | |
|-----------------------|------------------------------------|
| Product Specification | PS-19902-011-001, PS-19902-013-001 |
|-----------------------|------------------------------------|



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

19073 Series

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

| | |
|--------------|------------------|
| PremiumGrade | <u>640010100</u> |
|--------------|------------------|

Hand Crimp Tool for Avikrimp and Insulkrimp Terminals and Splices, 10-22 AWG and 6.0-0.5mm² (Rings, Spades, Hooks, Block Spades and Flanged Spades)
Crimp Head for the AT-200 Pneumatic Hand Tool

| |
|------------------|
| <u>640050100</u> |
|------------------|

ServiceGrade Hand 640160036
Crimp Tool for Field
Repair only, for
production use our
PremiumGrade Tool

This document was generated on 09/28/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19073-0173](#)