

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **0190740008**  
**Status:** **Active**  
**Overview:** Solderless Terminals  
**Description:** Krimptite Star Ring Tongue Terminal for 18-22 AWG Wire, Stud Size 10 (M5), Mylar Tape Carrier

**Documents:**

[3D Model](#) [Product Specification PS-19902-011-001 \(PDF\)](#)  
[3D Model \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Drawing \(PDF\)](#)

**Agency Certification**

CSA LR18689  
 UL E32244

**General**

Product Family Ring and Spade Terminals  
 Series [19074](#)  
 Crimp Quality Equipment Yes  
 Overview [Solderless Terminals](#)  
 Product Name Krimptite  
 Type Ring  
 UPC 800753078888

**Physical**

Barrel Type Closed  
 Insulation None  
 Material - Plating Mating Tin  
 Net Weight 0.436/g  
 Packaging Type Adhesive Tape on Reel  
 Stud Size 10 (M5)  
 Wire Size AWG 18, 20, 22

**Material Info**

Engineering Number SRA-129-10T

**Reference - Drawing Numbers**

Product Specification PS-19902-011-001



Series image - Reference only

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
 D(2021)4569-DC (8  
 July 2021)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[19074 Series](#)

**Application Tooling | [FAQ](#)**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

**Description**

**Product #**

ATP Crimp Dies  
 for the Tape Crimp  
 Module and ATP-101  
 & 301 Press

[190270071](#)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19074-0008](#)