

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0190750023**
Status: **Active**
Overview: Solderless Terminals
Description: InsulKrimp Steel Star Ring Tongue Terminal for 14-16 AWG Wire, Stud Size 10 (M5)

Documents:

3D Model	Product Specification PS-19902-011-001 (PDF)
Drawing (PDF)	Product Specification PS-19902-013-001 (PDF)
3D Model (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-19902-009-001 (PDF)	

Agency Certification

CSA	LR18689
UL	E32244

General

Product Family	Ring and Spade Terminals
Series	<u>19075</u>
Crimp Quality Equipment	Yes
Overview	<u>Solderless Terminals</u>
Product Name	InsulKrimp
Type	Ring
UPC	800753079823

Physical

Barrel Type	Closed
Color - Resin	Natural
Flammability	94V-0
Insulation	PVC
Material - Plating Mating	Tin
Net Weight	0.626/g
Packaging Type	Bag
Stud Size	10 (M5)
Wire Insulation Diameter	4.45mm
Wire Size AWG	14, 16

Material Info

Engineering Number	SRB-S-229-10X
--------------------	---------------

Reference - Drawing Numbers

Product Specification	PS-19902-009-001, PS-19902-011-001, PS-19902-013-001
-----------------------	---



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

19075 Series

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

Hand Crimp Tool	<u>640011900</u>
-----------------	------------------

Crimp Head for the	<u>640051900</u>
--------------------	------------------

AT-200 Pneumatic Hand Tool	
-------------------------------	--

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19075-0023](#)